

MICRONEL MINIATURE FANS AND BLOWERS

POWERING AIR FOR MEDICAL CARE


Micronel Fans and Blowers
Powerful, high airflow, quiet,
highly efficient


APPLICATIONS

- Mattress inflation for pressure sore prevention
- Mattress low air loss therapy for burns and skin therapy
- Mattress inflation (patient lifting & transport)
- Negative pressure wound therapy (VAC)
- Patient warming blankets
- External Cough Jacket Therapy for secretion clearance

PRODUCT FEATURES

- Brushless motor drives
- Vacuum and pressure up to 16000 Pa
- Flow rate up to 2000 l/min
- Compact and quiet
- 12 V_{DC} versions available
- Available with integrated electronic motor driver
- Energy saving


Micronel's high performance U-Line Radial Blowers are helping to enable the clinical advances in a variety of inflation related applications including air mattresses for the prevention of pressure sores and bedbound injury prevention, low air loss air circulation mattress toppers for burns patients, patient lifting and transport, negative pressure wound therapy (VAC), Patient warming blankets during surgery and high frequency chest oscillation cough therapy vests. Micronel's precision engineered compact blower products utilise the latest brushless motor technology to provide high pressure/suction combined with high airflow, low noise, low power consumption for portable applications combined with highest reliability and life expectancy.



U85MX

Most powerful blower,
where highest pressures
are needed!

Supply voltage	24 V _{DC}
Static pressure	12500 Pa
Freeflow	860 l/min
Motor controller	Integrated driver electronics
Typical applications	Rapid high pressure inflation of mattress chambers and external cough assist jackets



U85HL

Extremely powerful
blower, very versatile
and reliable!


Supply voltage	24 V _{DC}
Static pressure	11500 Pa
Freeflow	850 l/min
Motor controller	Integrated driver electronics
Typical applications	Air mattress inflation, patient moving and low air loss therapy



U51DL

Super compact,
powerful blower with
medical quality!

Supply voltage	12 and 24 V _{DC}
Static pressure	5600 Pa
Freeflow	510 l/min
Motor controller	Integrated driver electronics
Typical applications	Small, portable, quiet low air loss therapy requirements



U100H4

Super ruggedized
industrial, versatile
blower platform!

Supply voltage	24 V _{DC}
Static pressure	16000 Pa
Freeflow	865 l/min
Motor controller	Integrated driver electronics
Typical applications	IP sealed high pressure applications such as patient lifting and moving