

MICRONEL MINIATURE FANS AND BLOWERS

POWERING AIR FOR VACUUM HOLDING

Micronel Industrial Blowers
Powerful suction for a safe hold
in vacuum tables and conveyors

**SUCTIONING AND VACUUM APPLICATIONS**

Vacuum tables or suction belts are often found in printing houses or in the field of industrial manufacturing where a distortion-free condition of workpieces is required. The surface is equipped with a hole/slot pattern; the Micronel blower mounted on the bottom generates the vacuum through suction.

Due to the compact design and their possibility of being independently positioned, the powerful Micronel blowers are sure to impress and replace typical vacuum pumps.

Industrial solutions must be cost-effective and robust and have a long service life. The powerful axial and radial blowers from Micronel meet all these demands. Micronel blowers are used wherever sophisticated pressure and vacuum applications are needed. Typical areas of use with negative pressure are pick & place processes, vacuum conveyor technology, vacuum clamping plates / vacuum tables or anywhere requiring the extraction of dirt particles or fluids. Negative pressure or vacuum is used in manufacturing processes to fixate or transport production goods.


Micronel's precision-made miniature blowers are impressive due to their compact design and the use of the latest brushless motor technology in order to combine high pressure or negative pressure with high airflows. A low noise level, minimal energy consumption paired with unsurpassed reliability and an optimal service life distinguish the powerful Micronel products.



D604P

Cost effective blower
with high pressure
and flow rate!


Supply voltage	24 V _{DC}
Static pressure	823 Pa
Freeflow	1908 l/min
Motor controller	Integrated driver electronics



U85MX

Most powerful blower,
where highest pressures
are needed!


Supply voltage	24 V _{DC}
Static pressure	12500 Pa
Freeflow	860 l/min
Motor controller	Integrated driver electronics



U85HL

Extremely powerful
blower, very versatile
and reliable!

Supply voltage	24 V _{DC}
Static pressure	11500 Pa
Freeflow	850 l/min
Motor controller	Integrated driver electronics



U100HL

Super ruggedized
industrial, versatile
blower platform!

Supply voltage	24 V _{DC}
Static pressure	11400 Pa
Freeflow	865 l/min
Motor controller	Integrated driver electronics