

Scorpion Rework System - Selection Guide

Item	APR-1200-SRS	APR-1200-SRS-MOB	APR-1200A-SRS	APR-1200A-SRS-MOB
Image				
Rework Application	Standard	Mobile Device	Standard	Mobile Device
Placement Head	Manual	Manual	Motorized	Motorized
Placement Force Sensor	No	No	Yes	Yes
Placement Accuracy	0.0254 mm	0.0254 mm	0.0254 mm	0.0254 mm
Minimum Component Size	0.51 mm x 0.25 mm	0.51 mm x 0.25 mm	0.51 mm x 0.25 mm	0.51 mm x 0.25 mm
Minimum Component Pitch	0.3 mm	0.3 mm	0.3 mm	0.3 mm
Max PCB Size	343 mm x Open	305 mm x Open	343 mm x Open	305 mm x Open
Max PCB Thickness	6 mm	6 mm	6 mm	6 mm
Camera Field-of-View	45 mm x 57 mm	25 mm x 25 mm	45 mm x 57 mm	25 mm x 25 mm
Camera Resolution	720p + 1080p	1080p	720p + 1080p	1080p
Monitor Size	19 in.	22 in.	19 in.	22 in.
Remote Control	Analog	Analog	Digital	Digital
Country of Origin	USA	USA	USA	USA